

Silicon Photomultipliers (SiPM), High PDE and **Timing Resolution Sensors** in a TSV Package

J-Series SiPM Sensors

onsemi's J-Series low-light sensors feature a high PDE (photon detection efficiency) that is achieved using a high-volume, P-on-N silicon foundry process. The J-Series sensors incorporate major improvements in the transit time spread which results in a significant improvement in the timing performance of the sensor. J-Series sensors are available in different sizes (3 mm, 4 mm and 6 mm) and use a TSV (Through Silicon Via) process to create a package with minimal deadspace, that is compatible with industry standard lead-free, reflow soldering processes.

The J-Series Silicon Photomultipliers (SiPM) combine high performance with the practical advantages of solid-state technology: low operating voltage, excellent temperature stability, robustness, compactness, output uniformity, and low cost. For more information on the J-Series sensors please refer to the website.



ORDERING INFORMATION

See detailed ordering and shipping information on page 11 of this data sheet.

Table 1. GENERAL PARAMETERS

Parameter (Note 1)	Minimum	Typical	Maximum	Unit
Breakdown Voltage (Vbr) (Note 2)	24.2		24.7	V
Overvoltage (OV)	1		6	V
Operating Voltage (Vop = Vbr + OV))	25.2		30.7	V
Spectral Range (Note 3)	200		900	nm
Peak PDE Wavelength (λp)		420		nm
Temperature dependence of Vbr		21.5		mV/°C

^{1.} All measurements made at 21°C unless otherwise stated.

Table 2. PHYSICAL PARAMETERS

	3 mm	4 mm	6 mm
Parameter	30020, 30035	40035	60035
Active Area	$3.07\times3.07~\text{mm}^2$	$3.93\times3.93~\text{mm}^2$	6.07 × 6.07 mm ²
No. of Microcells	30020: 14,410 30035: 5,676	40035: 9,260	60035: 22,292
Microcell Fill Factor	30020: 62% 30035: 75%	40035: 75%	60035: 75%

^{2.} The breakdown voltage (Vbr) is defined as the value of the voltage intercept of a straight line fit to a plot of √I vs V, where I is the current and V is the bias voltage.

^{3.} The range where PDE > 2.0% at Vbr + 6.0 V.

Table 3. PERFORMANCE PARAMETERS

	300	035	400	035	600	035	Unit
	Overvoltage						
Parameter (Note 4)	+2.5 V	+6 V	+2.5 V	+6 V	+2.5 V	+6 V	Unit
PDE (Note 5)	38	50	38	50	38	50	%
Dark Count Rate	50	150	50	150	50	150	kHz/mm ²
Gain (anode-cathode)	2.9 × 10 ⁶	6.3 × 10 ⁶	2.9 × 10 ⁶	6.3 × 10 ⁶	2.9 × 10 ⁶	6.3 × 10 ⁶	
Dark Current - typical	0.23	1.9	0.35	3.0	0.9	7.5	μΑ
Dark Current – maximum	0.31	3.00	0.45	4.0	1.25	12.0	
Rise Time (Note 6) – anode-cathode output	90	110	90	110	180	250	ps
Microcell Recharge Time Constant (Note 7)	4	5	4	18 50		50	ns
Capacitance (Note 8) (anode output)	10	70	18	800	41	40	pF
Capacitance (Note 8) (fast output)	4	.0	70		160		pF
Fast Output Pulse Width (FWHM)	1	.5	1	.7	3.0		ns
Crosstalk	8	25	8	25	8	25	%
Afterpulsing	0.75	5.0	0.75	5.0	0.75	5.0	%
	30020						
			Overv	oltage			
Parameter (Note 4)		+2.5 V			+5 V		
PDE (Note 5)		30		38			%
Dark Count Rate		50		125			kHz/mm ²
Gain (anode-cathode)		1.0×10 ⁶			1.9×10 ⁶		
Dark Current - typical		0.1		0.45			μΑ
Dark Current – maximum	0.2			0.72			
Rise Time (Note 6) – anode-cathode output	130			160		ps	
Microcell Recharge Time Constant (Note 7)	15				ns		
Capacitance (Note 8) (anode output)	1040					pF	
Capacitance (Note 8) (fast output)	50				pF		
Fast Output Pulse Width (FWHM)	1.4				ns		
Crosstalk	2.5			7.5			%
Afterpulsing		0.75		5.0		%	

- 4. All measurements made at 21°C unless otherwise stated.
- 5. PDE does not contain afterpulsing or crosstalk, and is quoted at the peak wavelength (λ_p) .
 6. Measured as time to go from 10% to 90% of the peak amplitude and measured over a 1 Ω series output resistor.
 7. RC charging time constant of the microcell (τ) .
- 8. Capacitance values are for the complete TSV package.

Table 4. TVS PACKAGE SPECIFICS

		3 mm	4 mm	6 mm	
		30020, 30035	40035	60035	
Package Dimensions		3.16 × 3.16 mm ²	4.00 × 4.00 mm ²	6.13 × 6.13 mm ²	
Recommended Operating Temperature Range		-40°C - +85°C			
Soldering Conditions		Reflow Solder			
Cover Material		Glass			
Cover Refractive Index		1.53 @ 436 nm			
Moisture Sensitivity Level Tape & reel			MSL3*		
	Cut tape	MSL4*			
Maximum Average Current		10 mA	10 mA	15 mA	

^{*}Please refer to the TSV Handling and Soldering guide for more information on MSL for different delivery options.

PERFORMANCE PLOTS




Figure 1. Photon Detection Efficiency (PDE)

(MicroFJ-60035-TSV)




Figure 2. PDE vs. Overvoltage (MicroFJ-60035-TSV)




Figure 3. PDE vs. Crosstalk (MicroFJ-60035-TSV)




Figure 4. Gain vs. Overvoltage (MicroFJ-30035-TSV)




Figure 5. Fast Output Pulse Shape (MicroFJ-30035, MicroFJ-40035, MicroFJ-60035 Vbr + 2.5 V, 10 Ω Sense Resistor)





Figure 6. Standard Output Pulse Shape (MicroFJ-30035, MicroFJ-40035, MicroFJ-60035 Vbr + 2.5 V, 10 Ω Sense Resistor)

EVALUATION BOARD OPTIONS

SMA BIASING BOARD (MicroFJ-SMA-XXXXX)

The MicroFJ–SMA is a printed circuit board (PCB) that can facilitate the evaluation of the J-Series sensors. The board has three female SMA connectors for connecting the bias voltage, the standard output from the anode and the fast output signal. The output signals can be connected directly to a 50 Ω -terminated oscilloscope for viewing. The biasing and output signal tracks are laid out in such a way as to preserve the fast timing characteristics of the sensor.

The MicroFJ-SMA is recommended for users who require a plug-and-play set-up to quickly evaluate J-Series TSV sensors with optimum timing performance. The board also allows the standard output from the anode to be observed at the same time as the fast output. The outputs can be connected directly to the oscilloscope or measurement device, but external preamplification may be required to boost the signal. The table below lists the SMA board connections. The SMA board electrical schematics are available to download in the AND9808/D document.



MicroFJ-SMA-XXXXX			
Output	Function		
Vbias	Positive bias input (cathode)		
Fout	Fast output		
Sout	Standard output (anode)		

PIN ADAPTER (MicroFJ-SMTPA-XXXXX)

The TSV Pin Adapter board (SMTPA) is a small PCB board that houses the TSV sensor and has through-hole pins to allow its use with standard sockets or probe clips. This product is useful for those needing a quick way to evaluate the TSV package without the need for specialist surface-mount soldering. While this is a 'quick fix' suitable for many evaluations, it should be noted that the timing performance from this board will not be optimized and if the best possible timing performance is required, the MicroFJ-SMA-XXXXX is recommended. The SMTPA

circuit schematic is shown in Figure 8. Please consult the Readout and Biasing Application Note for further information on biasing. The SMTPA board electrical schematics are available to download in the AND9808/D.




Figure 7. Top View of the SMTPA Board Showing the Pin Numbering




Figure 8. SMTPA Circuit Schematic

MicroFJ-SMTPA-XXXXX			
Pin No.	Connection		
1	Anode		
2	Fast output		
3	Cathode		
4	Ground		
5	No connect		

CIRCUIT SCHEMATICS

An SiPM is formed of a large number (hundreds or thousands) of microcells. Each microcell (Figure 9) is an avalanche photodiode with its own quench resistor and a capacitively coupled fast output. These microcells are arranged in a close-packed array with all of the like terminals

(e.g. all of the anodes) summed together (Figure 10). The array of microcells can thus be considered as a single photodiode sensor with three terminals: anode, cathode and fast output, as shown in Figure 11.




Figure 10. Simplified Circuit Schematic of the onsemi SiPM showing only a 12 Microcell Example. Typically, SiPM Sensors have Hundreds or Thousands of Microcells

Figure 11. onsemi SiPM Component Symbol

TILING OF THE TSV PACKAGE

For the J-Series, **onsemi** has developed a market-leading, high-performance package using a TSV process. It is a chip-scale package that is compatible with lead-free, reflow soldering processes. The glass cover is ideal for coupling to scintillators or fibre optic elements.


The dead-space between the sensor active area and the edge of the package has been minimized, resulting in a package that can be tiled on 4 sides with high fill-factor.

This allows multiple sensors to be configured into unique layouts for a wide range of custom applications. The distance between sensor packages can be as little as 200 μm when tiled, but actual alignment and placement tolerances will depend on the accuracy of the user's assembly process. An Application Note is available that gives advice on creating arrays of the TSV sensors.

PACKAGE DIMENSIONS


(All Dimensions in mm)


MicroFJ-300XX-TSV



*The 'No Connect' pins are electrically isolated and should be soldered to a ground (or bias) plane to help with heat dissipation.

The MicroFJ-300XX-TSV-A2 CAD, and solder footprint, is available to download here.








PACKAGE DIMENSIONS

(All Dimensions in mm)

MicroFJ-40035-TSV







Pin Assignments			
Pin Number MicroFJ-40035-TS\			
B1, C1	Anode		
B4, C4	Fast output		
A1, D4	Cathode		
All others	No Connect*		


*The 'No Connect' pins are electrically isolated and should be soldered to a ground (or bias) plane to help with heat dissipation.


The MicroFJ-40035-TSV CAD, and solder footprint, is available to download here.

PACKAGE DIMENSIONS


(All Dimensions in mm)

MicroFJ-60035-TSV






BOTTOM VIEW




Pin Assignments			
Pin Number MicroFJ-60035-TSV			
C1, D1	Anode		
A1, F6	Cathode		
C6, D6	Fast output		
All others	No Connect*		


*The 'No Connect' pins are electrically isolated and should be soldered to a ground (or bias) plane to help with heat dissipation.

The MicroFJ-60035-TSV CAD, and solder footprint, is available to download <u>here</u>.





MicroFJ-SMA-60035 Board



The complete CAD for the SMA boards can be downloaded from the website: 3 mm, 4 mm and 6 mm versions.

MicroFJ-SMTPA-60035 Board

1.96 2.54 2.54 1.96 2.90 TOP VIEW SIDE VIEW

9.0±0.1

BOTTOM VIEW

The complete CAD for the SMTPA boards can be downloaded from the website: 3 mm and 6 mm versions.

ORDERING INFORMATION

Table 5. ORDERING INFORMATION

	Microcell Size	Sensor Active		Delivery Option
Product Code	(No. of Microcells)	Area	Description	(Note 9)
3 mm Sensors				
MICROFJ-30020-TSV	20 μm (14,410)	3.07 × 3.07 mm	4-side tileable, chip scale package with through-silicon vias (TSV)	TR1, TR
MICROFJ-SMA-30020-GEVB			TSV sensor mounted onto a PCB with three SMA connectors for bias, standard output and fast output	PK
MICROFJ-SMTPA-30020-GEVB			TSV sensor mounted onto a pin adapter board	PK
MICROFJ-30035-TSV	35 μm (5,676)		4-side tileable, chip scale package with through-silicon vias (TSV)	TR1, TR
MICROFJ-SMA-30035-GEVB			TSV sensor mounted onto a PCB with three SMA connectors for bias, standard output and fast output	PK
MICROFJ-SMTPA-30035-GEVB			TSV sensor mounted onto a pin adapter board	PK
4 mm Sensors				
MICROFJ-40035-TSV	35 μm (9,260)	3.93 × 3.93 mm	4-side tileable, chip scale package with through-silicon vias (TSV)	TR1, TR
MICROFJ-SMA-40035-GEVB			TSV sensor mounted onto a PCB with three SMA connectors for bias, standard output and fast output.	PK
6 mm Sensors				
MICROFJ-60035-TSV	35 μm (22,292)	6.07 × 6.07 mm	4-side tileable, chip scale package with through-silicon vias (TSV)	TR1, TR
MICROFJ-SMA-60035-GEVB			TSV sensor mounted onto a PCB with three SMA connectors for bias, standard output and fast output	PK
MICROFJ-SMTPA-60035-GEVB			TSV sensor mounted onto a pin adapter board	PK

^{9.} The two-letter delivery option code should be appended to the order number, e.g.) to receive a MICROFJ-60035-TSV on tape and reel, use MICROFJ-60035-TSV-TR. The codes are as follows:

PK = ESD Package

TR1 = Tape

TR = Tape and Reel

There is a minimum order quantity (MOQ) of 3000 for the tape and reel (TR) option. Quantities less than this are available on tape (-TR1). The TR option is only available in multiples of the MOQ.

SensL is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative